

INSTRUCTION MANUAL

(NL) Gebruikte symbolen


(GB) Safety Precautions / (FR) Symboles utilisés / (DE) Verwendete Symbole / (PL) Stosowane symbole / (NO) Brukte symboler / (DK) Brugte symboler / (SE) Använda symboler / (FI) Käytetyt symbolit / (IT) Simboli usati / (ES) Símbolos empleados / (CZ) Použité symboly / (PT) Símbolos utilizados / (GR) Χρησιμοποιούμενα σύμβολα



220-240V~
50Hz



IP20 CE UK CA



Dept DL White 91105
Dept DL Black 91106
Dept DL Gold 98849

<p>1.</p>	<p>2.</p> <p>ø80mm</p>	<p>3.</p>
<p>4.</p> <p>INPUT: AC220~240V</p>	<p>5.</p> <p>FREE SPACE ±10cm</p>	<p>6.</p> <p>Warning: When replacing a halogen lamp, wait for it to cool, for a minimum of 5 minutes</p>
<p>7.</p>	<p>Overall Sizes:</p> <p>92mm ø88mm</p>	